

## Outdoor Sensor Light



- Sensing angle up to 120 degrees
- Sensing range up to 12 m
- Sensor can be pointed in the direction required
- Manual override - light can be switched to stay on
- Selectable Motion Timer: 1, 5, or 10 minutes
- Selectable timer - choose how long you wish the light to remain on after detecting movement
- Dual pulse technology - minimise false triggering
- Dusk to dawn operation - will not come on during the day
- Bulbs - 2 x PAR38 150 W bulbs
- Bulbs - Screw-type bulbs



**ndis**

**Item Code:**

05\_098800044\_0103\_1\_2

Click [here](#) for more information

### Compliance

No applicable compliance standard

## Warranty Information

- 1 Year

| Code      | Display Name                                                |
|-----------|-------------------------------------------------------------|
| DLG272215 | Outdoor Sensor Light - Twin 150watt Sensor Light - 12metres |