



ELECTRIC SHOWER TROLLEY

The Aspire Electric Shower Trolley facilitates ergonomic showering for both caregivers and patients. Its soft patient surface and electric positioning enhance comfort and safety. Constructed from stainless steel, it maximizes durability and supports a high safe working load, accommodating a wide range of patient needs.



Hand Control
Can be mounted on all sides of the trolley in the integrated siderail notches



Platform Extension
Offers the option to fit a longer padded liner for taller users



Removable Battery
Easy swap overs allow for spare battery charging and constant uptime



1 YEARS WARRANTY
Components, Hand Control & Cables

5 YEARS WARRANTY
Frame

3 YEARS WARRANTY
Electronics



Maximum Total Load (Patient & Water)

Australia
1300 133 120 | aspirecare.com.au

United Kingdom
01622 541235 | aidacare.co.uk

Adjustable Side Rails offer three different positions



1. Upright for safety



2. Midway for carer washing access



3. Lowered for gap-free transfers

Accessible Height Range 460mm low height enables standing transfers while the 900mm maximum height enables ergonomic carer provision

Electric Adjustable Backrest and Tilt Angle improves patient comfort, visibility and confidence when being transported and assists with drainage

Stainless Steel Frame durable and strong design for asset longevity

Soft Shower Liner designed to enhance patient comfort during showering or care, contributing to a better patient experience



High Visibility Adjustments
Bright adjustment points are simple and intuitive to operate




Middle Access Zones
Improve carer ergonomics and patient cleaning access

OPTIONAL ACCESSORIES



Extended Length Liner
2100L x 600W | BTS148120



Accessory Basket
BTS148130



Shower Head Holder
BTS148125

ELECTRIC SHOWER TROLLEY	Overall Height	Overall Length	Overall Width	Patient Surface Length	Patient Surface Width	Patient Surface Height	Backrest Range	Tilt	Castor Size	Total Weight
	mm / in	mm / in	mm / in	mm / in	mm / in	mm / in	deg	deg	mm / in	kg / lbs
BTS148112	720-1180/ 29-47	2005-2205/ 79-87	820/ 33	1855-2055/ 73-81	600/ 24	460-900/ 18-36	15°	3°	125/ 5	95/ 210

Range of motion dimensions are accurate to a +/-10mm tolerance

ASF.Y126.4.141124