

SCOOTER SELECTION GUIDE

Category	Scooter Code	Image	Notes
COMPACT	BOOT SCOOTER (SCT670613)		Exclusive
	BOOT SCOOTER SUPALITE (SCT670616)		Exclusive
	GO-GO® LX + CTS SCOOTER (SCT670612)		
	SONIC SCOOTER (SCT670665)		Exclusive
MEDIUM	QUEST FOLDING COMPACT SCOOTER (SCT670630)		
	GT SCOOTER (SCT670670)		DVA Exclusive
	PATHRIDER® 10 SCOOTER (SCT670615)		DVA
	PATHRIDER® 10 DXE SCOOTER (SCT670507)		DVA Exclusive
	VICTORY 10 LX SCOOTER (SCT670640)		DVA
	PATHRIDER® 130 XL PURSUIT SCOOTER (SCT670571 / SCT670575)		DVA Exclusive
	PATHRIDER® 140 XLE SCOOTER (SCT670505 / SCT670506)		DVA Exclusive
	RANGERIDER SCOOTER (SCT670581)		DVA Exclusive

Terrain	Battery	Max Range Per Charge	Safe Working Load
Level & smooth terrain. Short distances.	2x 12V. 12AH	11.5 km	118 kg
Level & smooth terrain. Short distances.	1x 24V. 12AH	18.5 km	120 kg
Level & smooth terrain. Short distances.	2x 12V. 18AH	17 km	136 kg
Level & smooth terrain. Short distances.	2 x 12V. 20AH	20 km	136 kg
For more varied terrain. Short to medium distances.	1x 24V. 11.5AH Li-Polymer	20 km	115 kg
For more varied terrain. Short to medium distances.	2 x 12V. 35AH	30 km	159 kg
For more varied terrain. Short to medium distances.	2x 12V. 31AH (40AH optional)	25 km	159 kg
For more varied terrain. Short to medium distances.	2x 12V. 40AH	39 km	181 kg
Handles rougher terrain well. Long distances.	2x 12V. 40AH	26 km	159 kg
Handles rougher terrain well. Long distances.	2x 12V. 55AH	25 km	159 kg
Handles rougher terrain well. Long distances.	2x 12V. 100AH	35 km	181 kg
Handles rougher terrain well. Long distances.	2 x 24V. 100AH	30 km	159 kg

Features
<ul style="list-style-type: none"> Up to 6km/h Disassembles for easy transport
<ul style="list-style-type: none"> Up to 6.5km/h Disassembles for easy transport Comfort Trac front & rear suspension (CTS)
<ul style="list-style-type: none"> Up to 6.4km/h Disassembles in easy steps
<ul style="list-style-type: none"> Up to 8.8km/h Great outdoor stability, ease of use and maximum value
<ul style="list-style-type: none"> Up to 6km/h Disassembles for easy transport Easy-to-grip tiller adjustment knob
<ul style="list-style-type: none"> Up to 10km/h Front & rear suspension
<ul style="list-style-type: none"> Up to 8.5km/h Comfort Trac front & rear suspension (CTS)
<ul style="list-style-type: none"> Up to 10km/h Front & rear suspension Pneumatic tyres
<ul style="list-style-type: none"> Up to 9km/h Front & rear suspension Upgrade to 70AH batteries (x2) for improved performance
<ul style="list-style-type: none"> Up to 10km/h Front & rear suspension Upgrade to 100AH batteries (x2) for improved performance
<ul style="list-style-type: none"> Up to 10km/h Front & rear suspension High performance and 13" pneumatic tyres
<ul style="list-style-type: none"> Up to 10km/h Front & rear suspension High performance and 14.5" pneumatic tyres



Aidacare works closely with Pride Australia to offer a comprehensive line of mobility products to help our customers lead the most active, independent lifestyles.

- Pride Scooter products are all registered in the ARTG
- Please always read and understand your owners handbook before operating your new mobility scooter
- Please take care to observe safety and the speed limit requirements of your state



- Comfortable front-mounted post seat
- Back-lit battery gauge on monitor
- Front basket as standard
- Sleek & sporty design
- LED headlight, tail light and indicators on some models
- Low profile, puncture proof tyres or pneumatic tyres

SAFE USE VIDEO

There are a few safety considerations we'd like you to understand before operating your device. We strongly recommend all new mobility device customers watch our 7 minute YouTube video, 'Getting to Know your Power Mobility Device'.



Scan the QR code or visit the 'videos' page on our website.

SCOOTER ACCESSORIES

FLAG SCA668370	SADDLEBAG SCA668398	REAR POD SCA668399
SUN CANOPY SCA668375	REAR BASKET SCA668180	CANE HOLDER SCA668230
CUP HOLDER SCA668170	DUST COVER SCA668210	MIRROR SCA668300
OXYGEN BOTTLE HOLDER SCA668330	SCOOTER BAG + L PIECE SCA668340	WALKER HOLDER SCA668390

COMPATIBILITY MATRIX

Scan the QR code to view full range of Mobility Scooter Accessories and their compatibility.



MOBILITY SCOOTER SELECTION GUIDE



BOOT SCOOTER
SCT670613

Exclusive



- Feather touch disassembly for easy transportation & storage
 - Front-mounted post seat with arm rests
 - Easy to remove rechargeable battery
 - Soft and easy to adjust tiller
 - Modular design for easy servicing
- Colour: Red
Length: 1003 mm
Width: 495 mm
Product Weight: 45.6 kg (inc. batteries)
Maximum Speed: 6.4 km/h
Range: 11.5 km
Battery Size: 2 x 12V. 12 AH

SWL 118kg

SONIC SCOOTER
SCT670665

Exclusive



- Disassembles into 5 light weight pieces
 - Portable and durable scooter
 - Puncture-proof tyres
 - LED headlights and brakelights
 - Detachable battery with easy access
 - Adjustable angle tiller with delta
- Colour: Red
Length: 1040 mm
Width: 495 mm
Product Weight: 52 kg (incl batteries)
Maximum Speed: 6.8 km/h
Range: 20 km
Battery Size: 2 x 12V. 20AH

SWL 136kg

PRIDE PATHRIDER® 10 SCOOTER
SCT670615



- High performance, sleek and sporty
 - Low profile, puncture proof tyres
 - Back lit battery gauge
 - Front-mounted post seat with armrests
 - Front-position seat rotation
 - Wrap around easy drive tiller
- Colour: Blue
Length: 1190 mm
Width: 565 mm
Product Weight: 63.5 kg
Maximum Speed: 8.5 km/h
Range: 21 km
Battery Size: 2 x 12V. 31AH (40AH option)

SWL 159kg DVA

PATHRIDER® 130 XL PURSUIT
SCT670571 - RED, SCT670575 - YELLOW

Exclusive



- High performance, sleek and sporty
 - Large 13" pneumatic tyres
 - LED headlights, brakelights & indicators
 - Armrests, head rest & lumbar support
 - Rugged front and rear suspension
- Colour: Red
Length: 1359 mm
Width: 635 mm
Product Weight: 109 kg (incl batteries)
Maximum Speed: 10 km/h
Range: 25 km
Battery Size: 2 x 12V. 55AH

SWL 159kg DVA

WHILL MODEL C2 POWER WHEELCHAIR
PWS655320



- Omni-wheels for tight turning radius
 - Electromagnetic brakes provide safe stopping, even on inclines
 - Adjustable seat height, back support
 - Control remotely with iPhone/Android
 - Anti-sway system
- Colour: Black
Length: 990 mm
Width: 450 mm
Product Weight: 52 kg
Maximum Speed: 8 km/h
Range: 16 km
Battery Size: Lithium-ion (25.2V. 10Ah)

SWL 114kg

PRIDE IGO FOLDING POWER WHEELCHAIR
PWS654175



- Quickly folds in 5 easy steps
 - Unique seating for added comfort
 - Front suspension
 - Large, secure storage compartment
 - Easy-to-use VR2 controller
- Length & Width: 875 x 600 mm
Maximum Speed: 5.95 km/h
Product Weight: 19.8 kg
Seat Width: 470 mm
Battery Size: 2 x 6.6 Ah Lithium Ion

SWL 135kg

BOOT SCOOTER SUPALITE
SCT670616

Exclusive



- Disassembles into 6 lightweight pieces
 - Compact, foldable seat with armrests
 - Easy-to-grip tiller adjustment knob
 - Stable front frame-mounted seat post
 - Standard front basket provides storage
- Colour: White
Length: 1022 mm
Width: 480 mm
Product Weight: 34 kg (incl batteries)
Maximum Speed: 6.5 km/h
Range: 18.5 km
Battery Size: 1 x 24V. 12AH Lithium Ion

SWL 120kg

PRIDE QUEST FOLDING SCOOTER
SCT670630



- Sleek, stylish and easy to operate
 - Folded & ready for transport in 3 steps
 - Can be stowed upright or laid down
 - Great performance, indoors and out
 - Articulated front end
 - Front and rear LED headlights
- Colour: As Shown
Length: 930 mm
Width: 485 mm
Product Weight: 23.5 kg
Maximum Speed: 6 km/h
Range: 20 km
Battery Size: 1 x 24V (11.5 AH) Li-Polymer

SWL 115kg

PRIDE PATHRIDER® 10 DXE
SCT670507

Exclusive



- New style front tiller with LED lights
 - Comfortable high back seat
 - USB charging point for devices
 - 10" pneumatic tyres
 - Integrated storage space with cup holder built inside.
- Colour: Blue
Length: 1194 mm
Width: 560 mm
Product Weight: 68 kg
Maximum Speed: 10 km/h
Range: 39 km
Battery Size: 2 x 12V. 40AH

SWL 181kg DVA

PRIDE PATHRIDER® 140 XLE
SCT670505 - YELLOW, SCT670506 - RED

Exclusive



- New advanced LCD panel display
 - High performance ride quality
 - Large 13" pneumatic terrain-gripping low-profile tyres
 - Directional signals and large lower headlight for pathway illumination
- Colour: Yellow or Red
Length: 1422 mm
Width: 692 mm
Product Weight: 125 kg
Maximum Speed: 10 km/h
Range: 35 km
Battery Size: 2x 12V. 100AH

SWL 181kg DVA

PRIDE LITESTREAM® CARBON
PWS654185



- Lightweight carbon fibre frame
 - 120cm turning radius
 - Under seat pouch for extra storage
 - Optional manual setting
 - Folds for easy transport
- Colour: Black
Length: 930 mm
Width: 570 mm
Product Weight: 16 kg (excl battery)
Maximum Speed: 6 km/h
Range: 15 km
Battery Size: 24V. 12Ah Lithium Ion

SWL 136kg

PRIDE GO CHAIR - NEXT GENERATION (REAR WHEEL DRIVE)
PWS654200RE



- Disassembling compact design
 - Tight turning radius
 - 5-point swivel seat with latch release, 52cm lap belt,
- Length & Width: 838 x 574 mm
Maximum Speed: 5.95 km/h
Product Weight: Heaviest Part 16.3 kg
Seat Width: 460 mm
Range: 14 km
Battery Size: 2 x 12V. 18AH deep-cycle

SWL 136kg

PRIDE GO-GO® LX + CTS SCOOTER
SCT670612



- Comfort-Trac Suspension
 - Lightweight mobility scooter
 - Disassembles into 5 pieces for easy transportation and storage
 - Easy to remove rechargeable battery
 - Soft and easy to adjust tiller
- Colour: Red
Length: 1040 mm
Width: 520 mm
Product Weight: 39.5 kg
Maximum Speed: 6.4 km/h
Range: 17 km
Battery Size: 2 x 12V. 18AH

SWL 136kg

GT SCOOTER
SCT670670

Exclusive



- Advanced suspension for a smooth ride
 - Front and rear LED lighting
 - Directional signals
 - Deluxe tiller with USB charger
 - Cup holder
- Colour: Red
Length: 1200 mm
Width: 605 mm
Product Weight: 103 kg (incl batteries)
Maximum Speed: 10 km/h
Range: 30 km
Battery Size: 2 x 12V. 35AH

SWL 159kg DVA

PRIDE VICTORY 10 LX SCOOTER
SCT670640



- Comfort-Trac front and rear suspension
 - Sleek, modern design
 - Feather-touch disassembly for frame separation with only one hand
 - Full LED lighting package includes curb and rear lights and directional signals
- Colour: Red
Length: 1194 mm
Width: 565 mm
Product Weight: 120 kg
Maximum Speed: 9 km/h
Range: 26 km
Battery Size: 2 x 12V. 40AH

SWL 181kg DVA

PRIDE RANGERIDER
SCT670581

Exclusive



- Limited recline, black vinyl, high-back seat, lumbar support
 - Flip-up height and angle adjustable armrests
 - CTAS suspension with adjustable shock absorbers
 - Reversing sensors, LED light
- Length: 1560 mm
Width: 830 mm
Maximum Speed: 10 km/h
Range: 30 km
Battery Size: 2 x 24V. 100AH

SWL 159kg DVA

PRIDE JAZZY SELECT 6 (MID WHEEL DRIVE)
PWS654242



- Maximum front stability and in-line motor technology
 - 6" front and rear castors
 - Height and depth adjustable foot platform
- Length & Width: 900 x 600 mm
Product Weight: 75 kg
Maximum Speed: 6 km/h
Seat Width: 460 mm
Range: 21 km
Battery Size: 2 x 12V. deep-cycle

SWL 136kg



To view more mobility aids or complex rehab power chairs, scan the QR code or visit our website



◀ Aspire VOGUE Carbon Fibre Walker